



### 1.0 SCOPE

This standard specifies the general requirements for the packaging of the 90170 seriesstrain relief used with QF50 products.

### 2.0 PURPOSE

The purpose of this specification is to assure that all product shipped from Molex arrives damage free and in a manner which allows ease of handling, storage and distribution.

### **3.0 GENERAL PACKAGING INFORMATION**

- The recommended carton closure is tape.
- This document details component quantities required for the packaging of one Standard Packaging Quantity (SPQ),the Minimum Order Quantity (MOQ) and combinations of these.
- The shipping weight for a carton should not exceed 15kg.
- For carton box dimensions see E-96707-001

| REVISION: | ECR/ECN INFORMATION:       | TITLE: OF5            | 0 LOW PROFILE       |               | SHEET No.            |
|-----------|----------------------------|-----------------------|---------------------|---------------|----------------------|
|           | <u>EC No:</u> IPG2012-1068 | •                     | <b>FRAIN RELIEF</b> |               | <b>2</b> of <b>5</b> |
| Α         | <u>DATE:</u> 14 Jun 2012   | PACKAG                | ING SPECIFICAT      | ION           | 2 01 3               |
| DOCUMENT  | NUMBER:                    | CREATED / REVISED BY: | CHECKED BY:         | APPR          | OVED BY:             |
| P         | K-90170-001                | S.McGreevy            | D.Maher             | E.            | Folan                |
|           |                            |                       | TEMPLATE FILENAME:  | PACKAGING_SPE | C[SIZE_A4](V.1).DOC  |

## 4.0 PACKAGING OF 90170 PRODUCT

The first stage in packaging of the strain relief parts is to place a defined quantity of the part number to be packaged into a plastic bag (99990136). Quantities per bag for each product can be found in Table 1 below.

| Part Number | Circuit Size | Bag Part No. | Quantity per Bag<br>(SPQ) | MOQ  | Bags per<br>MOQ |
|-------------|--------------|--------------|---------------------------|------|-----------------|
| 90170-0010  | 10           | 99990136     | 1330                      | 6650 | 5               |
| 90170-0014  | 14           | 99990136     | 1050                      | 5250 | 5               |
| 90170-0016  | 16           | 99990136     | 910                       | 4550 | 5               |
| 90170-0020  | 20           | 99990136     | 770                       | 3850 | 5               |
| 90170-0026  | 26           | 99990136     | 630                       | 3150 | 5               |
| 90170-0030  | 30           | 99990136     | 560                       | 2800 | 5               |
| 90170-0034  | 34           | 99990136     | 490                       | 2450 | 5               |
| 90170-0040  | 40           | 99990136     | 420                       | 2100 | 5               |
| 90170-0050  | 50           | 99990136     | 350                       | 1750 | 5               |
| 90170-0060  | 60           | 99990136     | 280                       | 1400 | 5               |
| 90170-0064  | 64           | 99990136     | 280                       | 1400 | 5               |

Table 1, SPQ& MOQ values for each product

For each part number there is a Minimum Order Quantity. This MOQ and the number of bags required to provide the MOQ are also detailed in Table 1. When packaging into carton boxes the shipping specialist will endeavor to keep the packaging requirements at a minimum to keep freight expenses as low as possible.

In some instances an order may be comprised of multiples of MOQ with additional multiples of SPQ. For example, part number 90170-0020 (highlighted) has an MOQ of 5 bags of parts or 3850 pieces. A customer orders 4620 pieces in month 1 and 9240 pieces in month 2. These orders are made up of 6 & 12 SPQ units respectively.

In the case of the first order, the shipping specialist will use a carton (96707-0001) for 5 of the bags and the smaller (96707-0003) carton for the remaining bag. Any excess space inside the second carton will be filled with packaging space filler.

In the case of the second order, the shipping specialist would use a larger carton (96707-0007) for 10 of the bags and a (96707-0003) carton for the remaining 2 bags. Again, any excess space would be filled with a space filling material.

The above are only examples of how the product can be packaged. The shipping specialist will decide on the appropriate packaging depending on the actual quantities to be shipped.

| REVISION: | ECR/ECN INFORMATION:     | TITLE: OF5            | 0 LOW PROFILE       |               | SHEET No.            |
|-----------|--------------------------|-----------------------|---------------------|---------------|----------------------|
| Α         | EC No: IPG2012-1068      | · ·                   | <b>TRAIN RELIEF</b> |               | <b>3</b> of <b>5</b> |
| Γ         | <u>DATE:</u> 14 Jun 2012 | PACKAG                | ING SPECIFICAT      | ION           | 0 01 0               |
| DOCUMENT  | NUMBER:                  | CREATED / REVISED BY: | CHECKED BY:         | APPR          | OVED BY:             |
| P         | K-90170-001              | S.McGreevy            | D.Maher             | E.            | Folan                |
|           |                          |                       | TEMPLATE FILENAME:  | PACKAGING_SPE | C[SIZE_A4](V.1).DOC  |



# **PACKAGING SPECIFICATION**

### **5.0 WEIGHTS AND MEASURES**

### **Box dimensions:**

The Carton Boxes have the following outer dimensions:

| Box Part No. | Maximum<br>Outside<br>Length<br>(mm) | Maximum<br>Outside<br>Width<br>(mm) | Maximum<br>Outside<br>Depth<br>(mm) |
|--------------|--------------------------------------|-------------------------------------|-------------------------------------|
| 96707-0001   | 370.94                               | 183.94                              | 191.87                              |
| 96707-0003   | 371.94                               | 183.94                              | 99.88                               |
| 96707-0007   | 371.94                               | 371.94                              | 191.87                              |

Table 2, Box Dimensions

### Box weights:

It is not possible to give values for the weights of boxes where individual or multiple SPQ quantities are contained in a box. The following table gives an estimated weight of an MOQ and double MOQ shipping carton (MOQ using 96707-0001 & double MOQ using 96707-0007). Weights are based on volumetric measurement of 3D Cad data and specified density of plastic and measured weights of listed carton boxes. 3D Cad information may vary slightly from actual parts so specified weights are an estimate only.

| Part Number | Calculated<br>Weight (kg)<br>MOQ (96707-0001) | Calculated<br>Weight (kg)<br>2x MOQ (96707-0007) |
|-------------|---|--|
| 90170-0010  | 3.1kg   | 6.0kg  |
| 90170-0014  | 3.0kg   | 5.8kg  |
| 90170-0016  | 2.85kg  | 5.5kg  |
| 90170-0020  | 2.8kg   | 5.4kg  |
| 90170-0026  | 2.75kg  | 5.35kg   |
| 90170-0030  | 2.75kg  | 5.3kg  |
| 90170-0034  | 2.65kg  | 5.15kg   |
| 90170-0040  | 2.6kg   | 5.1kg  |
| 90170-0050  | 2.65kg  | 5.1kg  |
| 90170-0060  | 2.5kg   | 4.8kg  |
| 90170-0064  | 2.6kg   | 5.1kg  |

Table 3, Estimated Carton Weights for MOQ and 2x MOQ volumes

| REVISION: | ECR/ECN INFORMATION: | TITLE: QF5            | 0 LOW PROFILE       |               | SHEET No.            |
|-----------|----------------------|-----------------------|---------------------|---------------|----------------------|
| ٨         | EC No: IPG2012-1068  | ST                    | <b>TRAIN RELIEF</b> |               | <b>4</b> of <b>5</b> |
| Α         | DATE: 14 Jun 2012    | PACKAG                | ING SPECIFICAT      | ION           | 4 01 3               |
| DOCUMENT  | NUMBER:              | CREATED / REVISED BY: | CHECKED BY:         | APPRO         | OVED BY:             |
| P         | K-90170-001          | S.McGreevy            | D.Maher             | <b>E.</b> ]   | Folan                |
|           |                      |                       | TEMPLATE FILENAME:  | PACKAGING_SPE | C[SIZE_A4](V.1).DOC  |



## 6.0 LABELLING

The labels to be used are standard Molex Ireland 127mm x 76.2mm labels as specified in standard ES-40000-7012, as shown below. The Molex part no. and quantity will be clearly be marked on the label which will then be affixed to the outside of the packaging carton.

| DESCRIPTION     (a) QUANTITY   XXX     (b) INV CTRL DATE   XXX/XX/XX     (c) OUNTRY OF ORIGIN   IFEIand     (c) COUNTRY OF ORIGIN   IFEIand     (c) COUNTRY OF ORIGIN   IFEIand     (c) TACKING NO   XXXXXXXXXX     Mathematication - see www.molex.com   Image: Sundards     Parking Standards   (0)   VS     Mathematication - see www.molex.com   Image: Sundards   Image: Sundards     Mathematication - see www.molex.com   Image: Sundards   Image: Sundards     Mathematication - see www.molex.com   Image: Sundards   Image: Sundards     Mathematication - see www.molex.com   Image: Sundards   Image: Sundards   Image: Sundards     Mathematication - see www.molex.com   Image: Sundards   Im  | (1P) PART NUMBER   |                                 |  |                                 |
|--|--|---------------------------------|--|---------------------------------|
| (Q) QUANTITY   XXX     (12D) INV CTRL DATE   XXXX/XX/XX     (4L) COUNTRY OF ORIGIN   Ireland     (S) TRACKING NO   XXXXXXXXXX     Image: A constraint of the constraint o  |  |                                 |  | -                               |
| (4L) COUNTRY OF ORIGIN Ireland     (S) TRACKING NO     XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX   |  | ххх                             |  |                                 |
| (S) TRACKING NO XXXXXXXXX<br>REACH SVHC information - see www.molex.com<br>Packing Standards 0/0 VS<br>Eng.Nr. XXXXXXXXX XX<br>Molex<br>P/N XXXXXXXXXXX W  | (12D) INV CTRL DATE  | XXXX/XX/XX                      |  | -                               |
| REACH SVHC information - see www.molex.com Image: Comparison of the set of the s | (4L) COUNTRY OF ORIGI  | Ireland                         |  | 1                               |
| Packing Standards 0/0 VS   Eng.Nr. XXXXXXXXXXX X/X   Molex XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX  | (S) TRACKING NO  | xxxxxxxxxxx                     |  |                                 |
| Eng.Nr. XXXXXXXXX X/X   Molex XXXXXXXXXXXX www.molex.com   | REACH SVHC information   | - see www.molex.com             |  |                                 |
|  |  | ¥/¥                             |  | molex                           |
| MOLEX IRELAND LTD., SHANNON INDUSTRIAL ESTATE, SHANNON, CO.CLARE, IRELAND  | * * * * * * * *  | XXX                             |  | www.molex.com                   |
|  | MOLEVIDE   |                                 |  | •                               |
|  | MOLEX IKE  | LAND LTD., SHANNON INDUSTRIAL E | TATE, SHANNON, CO.CLARE, IRE                       | ELAND                           |
|  | ON:     ECR/ECN INFORMA       EC No:     IPG2012-10       DATE:     14 Jun 2012                  | TION: TITLE: QF                 | 50 LOW PROFILE                                     | SHEE<br>5 of                    |
| MENT NUMBER:     CREATED / REVISED BY:     CHECKED BY:     APPROVED BY   | <u>ON:</u> <u>ECR/ECN INFORMA</u><br><u>EC No:</u> <b>IPG2012-10</b><br><u>DATE:</u> 14 Jun 2012 | TION: TITLE: QF<br>68 PACKA     | 50 LOW PROFILE<br>STRAIN RELIEF<br>GING SPECIFICAT | <u>SHEE</u><br>ГІОN <u>5</u> об |